



# Warehousing & Logistics

Highlighted products which can help your warehouses & stores keep running smoothly & safely during these unprecedented times, all available with next working day delivery.

## Tape Dispenser

- Seal your carton or cardboard box quickly & reliably with this durable tape gun
- For use with 50mm width tape with a 75mm core diameter



528-5414

77,17 kr

## Scissors

- General use stainless steel bladed scissors ideal for cutting tape, card or paper
- Available in a choice of sizes from stock



509-9960 150mm  
 509-9948 200mm  
 182-442 220mm

487-101 205mm Heavy Duty Utility shears

96,79 kr  
 141,74 kr  
 55,28 kr  
 138,77 kr

## Packing Tapes

- A selection of popular 50mm width parcel & packing tapes suitable for use with tape dispensers
- We also stock over 50 options including widths from 9mm to 75mm from various well known brands



692-637 66m clear  
 198-6797 66m 'FRAGILE'  
 727-1280 100m clear  
 727-1287 100m brown

22,32 kr  
 70,18 kr  
 32,35 kr  
 32,35 kr

## Digital Platform Scales

- Battery & DC powered, compact moveable scales with 320 x 260mm weighing area - ideal for stores and smaller logistics operations
- Features adjusting program (CAL) and simple and convenient 2-key operation
- External universal mains adapter supplied



180-5337 20kg  
 180-5338 50kg

1194,27 kr  
 1194,27 kr

## 1D & 2D Barcode Scanner

- The OHV100 is a durable handheld barcode scanner supporting all standard 1D & 2D codes - inc. Aztec & Data Matrix
- Reads reliably up to 300mm distance due to a dual lens and a resolution of 1.2 million pixels
- Audible, tactile, and visual user feedback
- Protection degree IP54 - with options for USB or RS-232 leads
- Stand available - see 777-4935



777-4929 Scanner  
 777-4938 RJ-45 to USB flexi lead

4 890,00 kr  
 565,00 kr

## LabelWriter 450

- No expensive ink or toner needed - uses thermal printing technology
- Customise and print address, shipping, file folder and barcode labels with DYMO® Label™ v.8 software - all from your PC or Mac®
- Save time creating labels directly from text in popular software packages including from Microsoft®
- Eliminate the waste and hassles of sheet labels - print precise quantities of labels
- Prints crystal-clear barcodes, labels and graphics with 600 x 300dpi resolution
- Create custom labels from 60+ label styles and layouts
- Kit includes all you need to get started



701-9067

1 261,52 kr





**LabelManager 210D Kit**

- Great for labelling storage, racking, IT equipment, files & folders and creating information labels
- Store and quickly access up to 9 frequently-used labels
- Edit text easily via traditional keyboard layout and
- Create labels with 6 font sizes, 7 text styles, and 8 boxes plus underline
- Uses DYMO D1 labels in 6, 9, 12mm widths and multiple colours
- Kit includes printer, 12mm x 3m tape, soft carry case, EU mains AC adapter, 6 AA batteries and guide



860,15 kr



192-0482

**HyFlex® 11-618 Ultra-Lite Gloves**

- Lightweight work glove with Nylon liner and polyurethane coating, rated EN 388:2016 - 3121
- Superior comfort for all-day wearing and good sensitivity - only 0.8mm thick
- Offers good grip in dry or slightly oily conditions



56,87 kr



- 177-5842 Size 6
- 177-5843 Size 7
- 484-174 Size 8
- 484-130 Size 9
- 484-180 Size 10

56,87 kr

56,87 kr

56,87 kr

56,87 kr

56,87 kr

**Steel Sack Barrow**

- Ideal for high load capacities up to 200kg
- P handle can be used for one handed operation, when moving lighter loads
- Allows you to load the truck horizontally before being raised to the upright or tilted position
- Plate dimension 35x220mm



695,16 kr



669-3695

**Safety Glasses**

- Examples from our range of safety glasses for use in general material handling and other applications
- Tinted variants available
- Bolle options have anti-mist coating



30,09 kr

85,20 kr

116,12 kr

104-0947 Honeywell A800 Clear

295-823 Bolle Contour Clear

489-7094 Bolle Silium Clear

**Ear Defenders**

- Over ear protection with soft ear cushions offering superior comfort for all day use
- Lightweight and adjustable with padded headband for a secure and comfortable fit
- Offer protection of 28dB SNR (Single Number Rating) to EN 352-1 / CE-CAT III



76,49 kr



184-5934

**High Visibility Waistcoats**

- With reflective tape across the chest and waist
- Hook and loop front closure
- 100% polyester
- Generous fit, lightweight for free movement
- Orange also available on the website



64,31 kr

64,31 kr

64,31 kr



141-7767 S to M

141-7768 L to XL

141-7769 XXL to XXXL

**Ear Plugs**

- Soft foam earplugs are an ideal solution for operatives working in noisy conditions and offer an SNR of 37dB
- The 66cm corded options use a soft energy absorbing polymer foam, are washable with soap and water, and have an SNR of 26dB
- Both comply with EN 352-2



918-5703 37dB Orange, Box of 500 Pairs

689-9667 Corded Ear Plugs, 1 pair

503,89 kr

16,03 kr



### LIFELINE 4 Rope Pull Switches

- The Lifeline 4 cable/push button operated e-Stop system is often used on conveyors or large machinery
- Options of 75m & 125m span support
- Universal mounting and operation with cable status indicator on switch lid



Allen-Bradley

GuardMaster

<b>792-3115</b>	2NC 2NO (75m)	<b>1 319,77 kr</b>
<b>226-3180</b>	3NC 1NO (75m)	<b>1 319,77 kr</b>
<b>443-8061</b>	2NC 2NO (125m)	<b>1 806,00 kr</b>

### Portable Mobile Barrier

- Flexible barrier which can be set straight, curved or in a circle
- 4 metres long with 16 articulating panels
- 2 x non marking wheels and 4 locking straps to secure the barrier in a closed position



Rubbermaid  
Commercial Products

<b>794-8069</b>		<b>4 172,26 kr</b>
-----------------	--	--------------------

### Hazard & Lane Marking Tape

- Tough, durable warning and floor marking tape ideal for indicating lanes, hazards or in general flow management
- Full range of colours available on line from a choice of brands



RS  
PRO

<b>503-708</b>	Black & Yellow, 50mm x 100m reel	<b>52,73 kr</b>
<b>171-9692</b>	Yellow	<b>125,42 kr</b>
<b>171-9696</b>	Red	<b>125,42 kr</b>

### No Admittance Signage

- Prohibition Signs complying with the relevant UK and EC legislation - ISO7010
- Choice of either easy peel self-adhesive vinyl or 1.2mm thick rigid Polypropylene



RS  
PRO

<b>763-1881</b>	No Pedestrians 125x125mm	<b>69,17 kr</b>
<b>411-4024</b>	No Open Fire 200mm dia.	<b>56,87 kr</b>
<b>411-3223</b>	No Unauthorised Access 200mm dia.	<b>20,58 kr</b>
<b>813-4502</b>	No Smoking 100x100mm	<b>15,51 kr</b>

### Enclosed Emergency Stops

- Trigger action and mechanical latching operation
- Robust, Red 40mm mushroom heads
- Conform to the requirements of EN ISO 13850 & IEC 60947-5-5 which define the requirements of devices which initiate the emergency stop function



Schneider  
Electric

<b>330-8587</b>	E-Stop Station 2NC Turn to Release - XALK178F	<b>285,83 kr</b>
<b>609-4708</b>	E-Stop Station 1NO/1NC Turn to Release - XALK178E	<b>329,51 kr</b>

### Fixed LED High Bay Lighting

- Ideal for industrial and commercial applications such as factories and warehouses
- Great replacement for HID fittings, comes with an integral driver and flicker free technology
- Supplied with hanging hook and 2m of power flex



RS  
PRO

<b>176-8523</b>	100W 11,000lm	<b>1 258,26 kr</b>
<b>176-8521</b>	150W 16,500lm	<b>1 868,71 kr</b>
<b>176-8565</b>	200W 22,000lm	<b>2 491,74 kr</b>

### Ball Transfer Units

- Pre-lubricated ball transfer units which allow low friction movement or transfer of loads in all directions
- Available in a wide choice of load capacities, sizes and fixings
- Self-cleaning hole in base of bearing cup



ALWAYSE  
ENGINEERING LIMITED

<b>687-821</b>	15mm ball, flange mount	<b>75,90 kr</b>
<b>687-584</b>	19mm ball, flange mount	<b>51,25 kr</b>
<b>687-837</b>	22mm ball, flange mount	<b>100,34 kr</b>
<b>687-607</b>	32mm ball, flange mount	<b>91,31 kr</b>