



Make any workplace more coordinated


Find the right label for the right application



Files & Binders



Shipping



General Identification




Asset Tracking



Visitor Management



Mailing



Storage and Shelves




Chemical Storage



Utility Rooms



www.dymo.com




DYMO® D1 Standard labels offer the performance and variety you need for any labelling job.

- ▶ ‘Easy Peel’ for trouble-free application
- ▶ Wide range of colours and sizes for any labelling application
- ▶ Adheres to most clean and flat surfaces



DYMO® D1 Durable labels last on demanding surfaces to work overtime in tough conditions.

- ▶ Industrial-strength adhesive
- ▶ Indoor/outdoor use
- ▶ Scratch- and tear-resistant vinyl material

Typical D1 Standard label applications:



Typical D1 Durable label applications:



D1 Standard labels

Available in 6 mm, 9 mm, 12 mm, 19 mm, 24 mm
Material: POLYESTER (PET) - Thermal transfer printing technology - no ink or toner required

D1 STANDARD LABELS (7 m)	6 mm	9 mm	12 mm	19 mm	24 mm
ABC	S0720780	S0720680	S0720530	S0720830	S0720930
ABC	S0720770	S0720670	S0720500	S0720820	S0720920
ABC	S0720790	S0720730	S0720580	S0720880	S0720980
ABC	-	S0720710	S0720560	S0720860	-
ABC	-	S0720740	S0720590	S0720890	-
ABC	-	S0720720	S0720570	S0720870	S0720970
ABC	-	-	S0720610	S0720910	S0720940
ABC	-	S0720690	S0720540	S0720840	-
ABC	-	-	S0720510	-	-
ABC	-	-	S0720600	-	S0721000
ABC	-	S0720700	S0720550	S0720850	-
ABC	-	-	S0720520	-	-

D1 Durable labels

Available in 12 mm
Material: VINYL (PVC) - Thermal transfer printing technology - no ink or toner required

D1 DURABLE LABELS (3 m)		12 mm		D1 DURABLE LABELS (5.5 m)		12 mm					
ABC		1978366		ABC		1978364					
ABC		1978365									
ABC		1978367									
Multi-surface Household cleaners UV Light Moisture Temperature						Filing	Shelving	Inventory	Outdoor Recreation	Break/Storage room	†Check compatible DYMO® labelling machines on page 8.
Properties						Applications					
D1 Standard	-	-	✓	✓	-18°C to 90°C	✓	✓	-	-	-	All LabelManager™ label makers
D1 Durable	✓	✓	✓	✓	- 40°C to 80°C	✓	✓	✓	✓	✓	LabelManager™ 160, 280, 210D, 420P, PnP, 360D and MobileLabeler




DYMO® LW Paper labels: print one label or hundreds with ease.

- ▶ Direct thermal print technology provides clear text without messy, expensive ink or toner
- ▶ No sheet label jams, no layout hassle and no waste.
- ▶ Available in a variety of sizes for mailing, shipping and specialty applications

DYMO® LW Durable Labels offers stronger resistance on challenging surfaces.

- ▶ Industrial-strength adhesive
- ▶ Protective coated labels offering extra-resistance
- ▶ Scratch- and tear-resistant plastic material

Typical LW Paper label applications:



Typical LW Durable label applications:



LABEL TYPE	ITEM CODE	DESCRIPTION	SIZE (W x H mm)	LABELS/ROLL ROLLS/BOX	ADHESIVE	MATERIAL
STANDARD MAILING LABELS	S0722370	Standard Address Labels	28 x 89	130/roll - 2/box	Permanent	Paper
	1983173	Standard Address Labels	28 x 89	130/roll - 1/box	Permanent	Paper ECONOMY PACK
	1982991	Standard Address Labels	28 x 89	260/roll - 2/box	Permanent	Paper
	S0722380	Assorted Colour Labels	28 x 89	130/roll - 2/box	Permanent	Paper
	1983172	Large Address Labels	36 x 89	260/roll - 1/box	Permanent	Paper ECONOMY PACK
	S0722400	Large Address Labels	36 x 89	260/roll - 2/box	Permanent	Paper
	S0722410	Large Address Labels	36 x 89	260/roll - 1/box	Permanent	Transparent Plastic
	S0722520	Large Return Address Labels	25 x 54	500/roll - 1/box	Permanent	Paper
	S0929120	Square Multipurpose Labels	25 x 25	750/roll - 1/box	Removable	Paper
STANDARD SHIPPING LABELS	S0722430	Shipping / Name Badge Labels	54 x 101	220/roll - 1/box	Permanent	Paper
STANDARD MULTI-PURPOSE LABELS	S0947420	High Capacity Large Shipping Labels*	102 x 59	575/roll - 2/box	permanent	Paper
	S0904980	Extra Large Shipping Labels*	104 x 159	220/roll - 1/box	Permanent	Paper
	S0722530	Multi-Purpose Labels	13 x 25	100/roll - 1/box	Removable	Paper
	S0722550	Multi-Purpose Labels	19 x 51	500/roll - 1/box	Removable	Paper
STANDARD SPECIALTY LABELS	S0722540	Multi-Purpose Labels	32 x 57	1000/roll - 1/box	Removable	Paper
	S0722440	Large Multi-Purpose Labels	54 x 70	320/roll - 1/box	Permanent	Paper
	S0722460	Suspension File Labels	12 x 50	220/roll - 1/box	Permanent	Paper
	S0722470	LAF Labels Small	38 x 190	110/roll - 1/box	Permanent	Paper
	S0722480	LAF Labels Large	59 x 190	110/roll - 1/box	Permanent	Paper
	S0719250	CD/DVD Labels	57 mm Ø	160/roll - 1roll/box	Permanent	Paper
	S0722560	Small Name Badge Labels	41 x 89	300/roll - 1/box	Removable	Paper
	S0929100	Appoinment/Name Badge Labels	51 x 89	300/roll - 1roll/box	Removable	Paper
	S0929110	Large Name Badge Labels	62 x 106	250/roll - 1roll/box	Removable	Paper

*For use with LabelWriter™ 4XL only

LABEL TYPE	ITEM CODE	DESCRIPTION	SIZE (W x H mm)	LABELS/ROLL ROLLS/BOX	ADHESIVE	MATERIAL
LW DURABLE LABELS	1976200	LW Durable Labels	25 x 89	100/roll - 1/box	Permanent	Polypropylene with protective coating
	1933081	LW Durable Labels	25 x 89	350/roll - 2/box		
	1976411	LW Durable Labels	25 x 54	160/roll - 1/box		
	1933085	LW Durable Labels	19 x 64	450/roll - 2/box		
	1933083	LW Durable Labels	25 x 25	850/roll - 2/box		
	1933084	LW Durable Labels	57 x 32	800/roll - 1/box		
	1976414	LW Durable Labels	59 x 102	50/roll - 1/box		
	1933088	LW Durable Labels	59 x 102	300/roll - 1/box		
	1933087	LW Durable Labels	59 x 190	170/roll - 1/box		
	1933086	LW Durable Labels*	104 x 159	200/roll - 1/box		

*For use with LabelWriter™ 4XL only

	Multi-surface	Solvent Resistant	Moisture	Temperature	Mailing & Shipping	Name badges	Inventory	Floor Marking	Shelving	¹Check compatible DYMO® labelling machines on page 9.
										
	Properties				Applications					
LW Paper	-	-	-	-18° C to 25° C	✓	✓	-	-	-	All LabelWriter™ printers
LW Durable	✓	✓	✓	-18° C to 50° C	✓	-	✓	✓	✓	All LabelWriter™ printers*

*not recommended for use with the LabelWriter® 450 Duo

LW Labels

A visual guide to some of our most popular label shapes and sizes.




SMALL NAME BADGE



41 x 89 mm S0722560 (300 per roll)

ADDRESS



36 x 89 mm
S0722410 Clear | S0722400 White
28 x 89 mm
1983173 (130 per roll) | 1982991 (260 per roll)
89 x 36 mm 1983172 (260 per roll)



SHIPPING



54 x 101 mm S0722430 (220 per roll)



HIGH CAPACITY SHIPPING
For use with LabelWriter™ 4XL only
102 x 59 mm S0947420 (575 per roll)

SUSPENSION FILE



12 x 50 mm S0722460 (220 per roll)




EXTRA LARGE SHIPPING



For use with LabelWriter™ 4XL only
104 x 159 mm S0904980 (220 per roll)



APPOINTMENT / NAME BADGE



51 x 89 mm
S0929100 (300 per roll)

FILING / MEDIA STORAGE




57 mm diameter
S0719250 (160 per roll)



59 x 109 mm
S0722480 (110 per roll)


38 x 190 mm
S0722470 (110 per roll)

NAME BADGES



41 X 89 mm S0722560 (300 per roll)
62 x 106 mm S0929110 (250 per roll)

LARGE MULTI-PURPOSE



54 X 70 mm
S0722440 (320 per roll)



MULTI-PURPOSE



32 x 57 mm
S0722540 (1000 per roll)
Removable

19 x 51 mm
S0722550 (500 per roll)

25 x 25 mm
S0929120 (750 per roll)

13 x 25 mm
S0722530 (1000 per roll)



LabelManager™ Label Makers

Leave any project or task looking better than you found it.



Feature / Product	LabelManager 160	LabelManager 210D	LabelManager 280	LabelManager 420P	LabelManager 360D	LabelManager PnP	MobileLabeler™
ITEM #	S0946320	S0784440	S0968960	S0915490	S0879490	S0915390	1978247
Product Description	Easy-To-Use Label Maker with Fast-Formatting Keys	All-Purpose Label Maker with Large Graphical Display	Rechargeable Handheld Label Maker with PC or Mac® Connection	High-Performance Portable Label Maker with PC/Mac® Connection	Rechargeable Desktop Label Maker	Plug and Play Label Maker for PC or Mac®	Label Maker with Bluetooth® Connectivity
Print Resolution DPI	180	180	180	180	180	180	300
Printing System	Thermal Transfer	Thermal Transfer	Thermal Transfer	Thermal Transfer	Thermal Transfer	Thermal Transfer	Thermal Transfer
Label System	D1 Standard and Durable	D1 Standard and Durable	D1 Standard and Durable	D1 Standard and Durable	D1 / IND	D1 Standard and Durable	D1 Standard and Durable
Number of Print Lines	2	2	2*	4*	2	Unlimited	–
Label Widths	6, 9, 12 mm	6, 9, 12 mm	6, 9, 12 mm	6, 9, 12, 19 mm	6, 9, 12, 19 mm	6, 9, 12 mm	6, 9, 12, 19, 24 mm
Normal/Bold/Italic/Underline	√	√	√	√	√	√	√
Vertical Effect	√	√	√	√	√	√	√
Mirror Effect	–	√	√	√	√	√	√
Symbols Library	228	132	220*	325*	221	Unlimited*	Unlimited*
Number of Character Sizes	6	6	6*	7*	7	Unlimited*	Unlimited*
Keyboard Layout	QWERTY	QWERTY	QWERTY	ABC	QWERTY	–	–
Fast-Formatting Keys	√	–	√	–	–	–	–
Backlit Display	–	–	–	√	–	–	–
Fixed Length	–	√	√	√	√	√	√
Barcodes	–	–	12†	12†	-	-	12†
Label Cutter	Manual	Manual	Manual	Manual	Manual	Manual	Automatic
Battery Type	6 AAA	6 AA	Rechargeable	Rechargeable	Rechargeable	Rechargeable	Rechargeable
Computer Connectivity	–	–	PC/Mac®	PC/Mac®	PC/Mac®	PC/Mac®	PC, Mac®, Android™, iOS
Bluetooth connectivity	–	–	–	–	–	–	√

* Unlimited when connected to PC or Mac®
† Some barcodes may be printed directly from label maker without PC or Mac® connection.



LabelWriter™ Label Printers

Make any workspace more productive, efficient and professional.



Feature / Product	LabelWriter™ Wireless	LabelWriter™ 450	LabelWriter™ 450 Turbo	LabelWriter™ 450 Twin Turbo	LabelWriter™ 450 Duo	LabelWriter™ 4XL
CODE #		S0838810	S0838860	S0838910	S0838960	S0904960
Product Description	Cable-free convenience and easy network sharing using Wi-Fi®	Professional Label Printer for PC and Mac®	High Speed Label Printer for PC and Mac®	Dual-Roll Label Printer for PC and Mac®	Paper and Plastic Label Printer for PC and Mac®	Heavy-Duty High-Speed Label Printer
Capacity	Single Roll	Single Roll	Single Roll	Dual Roll	Single Roll + D1-tapes	Wide Format
Print Resolution (dpi)	600 x 300	600 x 300	600 x 300	600 x 300	600 x 300 (D1: 180)	600 x 300
Printing System	Direct Thermal	Direct Thermal	Direct Thermal	Direct Thermal	Direct Thermal Thermal Transfer	Direct Thermal
Print Speed (labels/min)	71*	51*	71*	71*	71*	53* (129 on high capacity labels)
Maximum Print Width (mm)	62	62	62	62	62	106
Label Types	LW + LW Durable	LW + LW Durable	LW + LW Durable	LW + LW Durable	LW + D1**	LW + LW Durable

* 4-line address label
** Not compatible with D1 Durables or LW Durables



Included with all DYMO® LabelWriter™ label printers:

Each LabelWriter™ printer comes with the latest DYMO® Label™ software that makes creating customised labels easy with text, images, pictures, date & time, serial numbers, and 20 different types of barcodes.



Create your own desktop mailing solution

Combine any LabelWriter™ label printer with any DYMO® USB digital postal or shipping scale to create a complete mailing or shipping system.



Environmentally friendly

All LabelWriter™ printers have automatic sleep mode – to conserve energy and reduce your costs.



	D1 Standard		D1 Durable		LW Paper		LW Durable		
DYMO Label	Filing & Sampling	General Identification	Asset Tracking	Utility Cupboards	Mailing & Shipping	Visitor Management	Floor Marking	Inventory	Shelving
Key Points of Difference	• Easy peel • Indoor usage • 5 sizes • 12 colours	• Industrial-strength adhesive • Ideal for Indoor & Outdoor usage • Scratch and tear-resistant material			• Paper labels • Variety of sizes • Simplify everyday labelling tasks		• Industrial-strength adhesive • Moisture & Solvent-resistant • Protective coating for extra-resistance • High volume per rolls for industrial use*		
Printing Technology	Thermal Transfer				Direct thermal				
Label Material	Continuous labels				Pre-sized labels				
	Polyester (PET)	Vinyl (PVC)			Paper		Polypropylene with protective coating		
Machine Compatibility	LabelManager™ and LabelWriter 450 Duo**				LabelWriter™**				

*on selected labels.
**Durable labels not recommended for use with the LabelWriter™ 450 Duo, LabelManager 500TS, LabelManager PnP Wireless

Notes

dymo.com

Newell Europe Sàrl
Chemin de Blandonnet 10
1214 Vernier - Switzerland

DYMO
newell
BRANDS
© 2017 Newell Brands