DYMO®

XTL™

Industrial Labelling Solution

SIMPLIFIES THE MOST COMPLEX LABELLING.

XTL™

WE BET YOU'VE NEVER EXPERIENCED INDUSTRIAL LABELLING THIS SIMPLE.

Jobsite tested and packed with features, the DYMO® XTL™ 300 and XTL 500 label makers help simplify industrial labelling for a more efficient, frustration-free experience. By incorporating cues from today's technology, XTL label makers offer a familiarity that makes using them easy. That's why over 80% of people who used an XTL label maker for eight weeks without any training said it performed better than their current label maker*. Built to meet your needs, DYMO XTL label makers offer the flexibility to print continuous tape, pre-sized labels, heat-shrink tubes and small format safety signage all from the same label maker. A full range of durable XTL labels are also available in a variety of materials and colours that fit with OSHA, ANSI and ISO colour standards for workplace communication and safety.

Read on to see how XTL label makers are redefining simplicity.

LIFE-LIKE ON SCREEN
PRINT PREVIEW

and colour display shows exactly how labels will look when applied to cables, pipes, panels, and more

** Based on in-field use study*

BUILT-IN LABEL ***APPLICATIONS***

simply select an application from the Home screen to get started quickly

TOUCH SCREEN

helps make label creation easier and faster

(available only on XTL 500)

PRE-LOADED LABEL TEMPLATES

create labels 3x faster* and ensure perfect formatting to save time.

Also includes pre-set layouts for almost 100 patch panel models to eliminate size and spacing guesswork.

ADDITIONAL FEATURES INCLUDE:

1. 3-Year Limited Warranty + 1 additional year upon registering online
2. Maximised print area helps reduce label waste
3. PC-connectivity to easily transfer labels to and from DYMO ID software for jobsite editing and printing
4. FREE DYMO ID software adds even more capability to your XTL label maker
5. Durable built-in cutter for fast label production
6. Impact-resistant rubber bumpers and wipe-clean keypad withstands harsh environments
7. On-screen label indicator automatically detects and displays the loaded label
8. Customisable printer settings eliminate unnecessary menus and steps

dymo.com

** when compared to creating labels on an XTL label maker without templates*

DYMO®

DYMO® ID - ACHIEVING LABELLING SIMPLICITY JUST GOT EASIER.

Using DYMO ID is easy thanks to a uniform experience that integrates the same great features found on your XTL™ label maker and packs them into a powerful PC-based software package. Once you've used an XTL label maker, learning to use DYMO ID will be a breeze. Available as a free download from dymo.com, DYMO ID will provide you with the functionality you need to tackle even the most complex labelling.

QUICKLY IMPORT DATA

to create a series of labels in just a few steps to eliminate manual entry, saving time and increasing productivity

OVER 200 PRE-LOADED SYMBOLS & IMAGES

or simply add a custom image to enhance communication and meet industry standards

SHEET LABELS

Quickly print XTL label maker Laminated Wire/Cable Wrap sheet labels directly to a laser printer

QUICK CUSTOMISATION & UPGRADES

Simply plug your XTL into a PC and use DYMO ID software to customize your preferences and keep it up to date

DYMO ID WORKS WITH THE FOLLOWING:

- XTL 300 Label Maker
- XTL 500 Label Maker
- XTL Laminated Wire/Cable Wrap Sheet Labels
- Works with Windows®7 and later

Available as a FREE download from www.dymo.com

XTL™

Selection Guide

	XTL™ 300	XTL™ 500
Printing System	Thermal Transfer	Thermal Transfer
Max Label Width	24 mm	54 mm
Labels Supported	DYMO XTL	DYMO XTL
Display	71.12 mm Colour	109.22 mm Colour Touch Screen
Print Speed (average)	23 mm/sec	28 mm/sec
Keyboard	QWERTY	QWERTY
Print DPI	300	300
Printable Lines	11	24
Barcodes Supported	Code 128 (Auto), Code 39, Code 39 Mod 43, EAN8, EAN13, UPC-A, Codabar, PDF-417, QR Code	Code 128 (Auto), Code 39, Code 39 Mod 43, EAN8, EAN13, UPC-A, Codabar, PDF-417, QR Code
Serialization	Yes	Yes
Cutter	Manual, Replaceable	Auto, Replaceable
Power Supply	Rechargeable Lithium Polymer Battery or AC Adapter	Rechargeable Lithium Polymer Battery or AC Adapter
Memory	41 MB	41 MB
Warranty	3 + 1 Year Limited	3 + 1 Year Limited
PC Connectivity	YES	YES
Software	DYMO ID, free download	DYMO ID, free download
Compatibility	Windows® 7 and later	Windows® 7 and later
Pack Contents	• DYMO XTL 300 Label Maker • AC Charging Adapter • USB Cable • Rechargeable Lithium Polymer Battery • (1) 24 mm x 7 m All-Purpose Vinyl, Black/White • Lanyard • Quick Start Guide • Software Download Card **Kit includes everything above, plus:** • Carrying Case • (1) 21 mm x 39 mm Laminated Wire/Cable Wrap, Black/White, 150 labels	• DYMO XTL 500 Label Maker • Carrying Case • AC Charging Adapter • USB Cable • Rechargeable Lithium Polymer Battery • (1) 54 mm x 7 m All-Purpose Vinyl, Black/White • (1) 38 mm x 39 mm Laminated Wire/Cable Wrap Black/White, 150 labels • Quick Start Guide • Software Download Card

LABEL APPLICATIONS		
110 & Terminal Blocks	✓	✓
Arc Flash		✓
Asset Tracking	✓	✓
Breaker	✓	✓
Cable Wrap	✓	✓
Distribution Panel	✓	✓
Flag	✓	✓
General Label	✓	✓
Heat-Shrink Tube	✓	✓
Materials Management	✓	✓
Patch Panel	✓	✓
Pipe Marking		✓
Quick Label	✓	✓
Safety		✓

DYMO®

XTL™

THE RIGHT LABEL

MORE **VERSATILITY.**

DELIVERING VERSATILITY AND DURABILITY, NO MATTER WHAT THE TASK.

DYMO XTL™ labels are durable and made for a variety of surfaces. Whether you are labelling to OSHA, ISO and ANSI colour standards or labelling in harsh conditions, DYMO XTL labels have you covered. Jobsite-tested and UL-recognised, these labels won't smear or fade. Compatible with DYMO XTL label makers.

ONE LABEL SYSTEM. **COUNTLESS APPLICATIONS.**



RECOMMENDED APPLICATIONS:

DYMO XTL 300

- General Idendification
- Barcodes (1D and 2D)
- Asset Tracking
- Wire and Cable Identification
- Networking Components Identification
- Facilities Identification

DYMO XTL 500

- General Idendification
- Barcodes (1D and 2D)
- Asset Tracking
- Data Communications Identification
- MRO / Facilities Identification & Communication

XTL LABELS

Industrial-strength labels withstand the toughest conditions – moisture, chemicals, a wide range of temperatures, UV light and more.

- Durable thermal transfer printing technology – label text won't smear or fade
- Easy-to-peel split back design and pre-sized labels make applying labels quick and easy

ALL-PURPOSE VINYL

- Moisture, chemical and UV resistance makes vinyl ideal for indoor/outdoor use
- Wide range of colours that fit with OSHA, ANSI and ISO colour standards to enhance workplace communication and safety
- UL recognised as a component to UL 969

FLEXIBLE CABLE WRAPS

- For labelling wires, cables and rounded surfaces, flexible nylon material is designed to conform and stick
- Tear-proof material resists damage when pulled through tight spaces or conduits
- UL recognised as a component to UL 969

LAMINATED WIRE/CABLE WRAPS

- Pre-sized wire/cable wraps with laminated overwrap protect printed areas from oil, chemicals, moisture, abrasion and fading
- Also available in sheet label formats for high-volume installations
- UL recognised as a component to UL 969

PRE-SIZED SAFETY LABELS

- Specific labels with coloured headers including labels pre-printed with DANGER and NOTICE headers for on-demand printing of small format safety signage
- UL recognised as a component to UL 969

PERMANENT FLAT SURFACE

- For labelling panels, blocks, faceplates, shelves, bins, beams and more
- For labelling flat surfaces, a glossy finish leaves a professional look
- UL recognised as a component to UL 969

HEAT-SHRINK TUBES
(CONTINUOUS AND PRE-SIZED)

- Heat-Shrink Tubes provide insulation when shrunk down and ensure a secure fit on wires and cables with a 3:1 shrink ratio
- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5 (Class 1 & 3)
- UL recognised as a component to UL 224

PRE-SIZED LABELS

- Ideal for flat surface labelling like barcodes, faceplates, shelves, bins, beams and more
- Pre-Sized labels help facilitate batch label printing to improve productivity
- UL recognised as a component to UL 969

XTL LABELS: A VISUAL GUIDE

LABEL WIDTHS



ALL-PURPOSE VINYL COLOURS

PRE-SIZED LABELS

1868665
12 mm x 12 mm

1868666
12 mm x 25 mm

1868667
12 mm x 38 mm

PRE-SIZED SAFETY LABELS

1868715 /
51 mm x 102 mm



1868716 / 51 mm x 102 mm

PRE-SIZED HEAT-SHRINK TUBE



1868733 / 24 mm x 47 mm Black on White

LAMINATED WIRE/CABLE WRAPS



1868708 / 38 mm x 39 mm

PERMANENT FLAT SURFACE

1868736 / 9 mm Black on White

1868740 / 12 mm Black on Clear

THE RIGHT LABEL *FOR THE RIGHT APPLICATION.*

		All-Purpose Vinyl	Permanent Flat Surface	Flexible Cable Wrap	Heat-Shrink Tube *(continuous & pre-sized)*	Laminated Wire/Cable Wraps	Pre-Sized Labels	Pre-Sized Safety Labels
Surface	Flat	✓	✓	✓			✓	✓
	Wires & Cables	✓		✓	✓	✓		
	Curved	✓		✓				
	Flag	✓		✓				
	Textured	✓	✓	✓			✓	✓
Resistance	Heat/Cold	-40° to 60° C	-40° to 60° C	-40° to 60° C	Max 125° C	-40° to 60° C	-40° to 60° C	-40° to 60° C
	Outdoor	✓	✓				✓	✓
	UV Light	✓	✓	✓	✓	✓	✓	✓
	Oil	✓	✓		✓	✓	✓	
	Water	✓	✓		✓	✓	✓	✓
	Chemical	✓	✓		✓	✓	✓	
Industry Standards & Ratings	Colour	OSHA, ANSI, ISO colour standards						Coloured headers to comply with OSHA, ANSI, ISO colour standards
	UL Recognised as acomponent to	UL 969	UL 969	UL 969	UL 224	UL 969	UL 969	UL 969
	MIL-Spec & SAE				MIL-M-8153 MIL-STD-202G SAE-DTL-230535 (Class 1 & 3)			
	RoHS	✓	✓	✓	✓	✓	✓	✓

dymo.com

DYMO

CONTINUOUS & PRE-SIZED LABELS

All-Purpose Vinyl

Flexible Cable Wrap

Permanent Flat Surface

Heat-Shrink Tube (continuous)

Text Colour on Label Colour	Length	6 mm	9 mm	12 mm	19 mm	24 mm	38 mm	54 mm
ALL-PURPOSE VINYL								
ABC	7 m	-	-	1868741	1868742	1868743	1868744	1868745
ABC	7 m	-	-	1868746	1868747	1868748	1868749	1868750
ABC	7 m	-	-	1868751	1868752	1868753	1868754	1868755
ABC	7 m	-	-	1868756	1868757	1868758	1868759	1868760
ABC	7 m	-	-	1868761	1868762	1868763	1868764	1868765
ABC	7 m	-	-	1868766	1868767	1868768	1868769	1868770
ABC	7 m	-	-	1868771	1868772	1868773	1868774	1868775
ABC	7 m	-	-	1868776	1868777	1868778	1868779	1868780
ABC	7 m	-	-	1868781	1868782	1868783	1868784	1868785
ABC	7 m	-	-	1868786	1868787	1868788	1868789	1868790
ABC	7 m	-	-	1868791	1868792	1868793	1868794	1868795
ABC	7 m	-	-	1868796	1868797	1868798	1868799	1868800
ABC	7 m	-	-	1868801	1868802	1868803	1868804	1868805
PERMANENT FLAT SURFACE								
ABC	9.1 m	1868735	1868736	1868737	-	-	-	-
ABC	9.1 m	1868738	1868739	1868740	-	-	-	-
FLEXIBLE CABLE WRAP								
ABC	5.5 m	-	-	1868806	1868807	1868808	-	-
HEAT-SHRINK TUBE (CONTINUOUS)								
ABC	2.7 m	1868809	-	1868810	-	1868811	-	1868812*

**Tape length 1.8 m for #1868812 only*

For technical specifications on all DYMO XTL label types, please visit our website at www.dymo.com

Heat-Shrink Tube (pre-sized)

Pre-Sized Labels

Pre-Sized Safety Labels

Laminated Wire/Cable Wraps

Laminated Wire/Cable Wraps (sheet labels)

Text Colour on Label Colour	Item #	Label Width	Label Length	Labels / Cartridge	Compatible Label Maker
PRE-SIZED HEAT-SHRINK TUBE					
ABC	1868717	6 mm	34 mm	81	XTL 500
ABC	1868718	12 mm	34 mm	65	XTL 500
ABC	1868719	24 mm	34 mm	60	XTL 500
ABC	1868720	54 mm	34 mm	25	XTL 500
ABC	1868731	6 mm	47 mm	81	XTL 500
ABC	1868732	12 mm	47 mm	65	XTL 500
ABC	1868733	24 mm	47 mm	60	XTL 500
ABC	1868734	54 mm	47 mm	25	XTL 500
PRE-SIZED LABELS					
ABC	1868665	12 mm	12 mm	250	XTL 300, XTL 500
ABC	1868666	12 mm	25 mm	250	XTL 300, XTL 500
ABC	1868667	12 mm	38 mm	185	XTL 300, XTL 500
ABC	1868668	25 mm	25 mm	250	XTL 500
ABC	1868669	9 mm	25 mm	250	XTL 300, XTL 500
ABC	1868670	12 mm	19 mm	250	XTL 300, XTL 500
ABC	1868701	19 mm	25 mm	250	XTL 300, XTL 500
ABC	1868702	25 mm	51 mm	100	XTL 500
ABC	1868703	51 mm	76 mm	100	XTL 500
PRE-SIZED SAFETY LABELS (WITH COLOURED HEADERS)					
ABC	1868713	51 mm	102 mm	70	XTL 500
ABC	1868714	51 mm	102 mm	70	XTL 500
NOTICE ABC	1868715	51 mm	102 mm	70	XTL 500
⚠ DANGER ABC	1868716	51 mm	102 mm	70	XTL 500
LAMINATED WIRE/CABLE WRAPS					
ABC	1868704	21 mm	21 mm	250	XTL 300, XTL 500
ABC	1868705	21 mm	39 mm	150	XTL 300, XTL 500
ABC	1868706	21 mm	102 mm	75	XTL 300, XTL 500
ABC	1868707	38 mm	21 mm	250	XTL 500
ABC	1868708	38 mm	39 mm	150	XTL 500
ABC	1868709	38 mm	102 mm	75	XTL 500
ABC	1868710	51 mm	21 mm	250	XTL 500
ABC	1868711	51 mm	39 mm	100	XTL 500
ABC	1868712	51 mm	102 mm	70	XTL 500

LAMINATED WIRE/CABLE WRAPS (SHEET LABELS)

Text Colour on Label Colour	SKU #	Label Width	Label Length	Labels/Sheet	Sheets/Pack	Labels/Pack
ABC	1908552	24 mm	23 mm	96	27	2592
ABC	1908553	24 mm	42 mm	48	53	2544
ABC	1908554	24 mm	103 mm	16	63	1008
ABC	1908555	41 mm	23 mm	60	34	2040
ABC	1908556	41 mm	42 mm	30	34	1020
ABC	1908557	54 mm	23 mm	36	28	1008
ABC	1908558	54 mm	42 mm	18	56	1008

Windows is a registered trademark of Microsoft Corporation in the United States and other countries.

dymo.com

DISTRIBUTED BY/DISTRIBUÉ PAR: NEWELL EUROPE SARL, CHEMIN DE BLANDONNET, 101214 VERNIER, SWITZERLAND | REPRESENTED IN THE EU BY / REPRESENTE EN UE PAR: NWL BELGIUM SERVICES BVBA, INDUSTRIEPARK-NOORD 30, 9100 SINT-NIKLAAS – BELGIUM

A Newell Rubbermaid Brand

© 2015 Newell Rubbermaid Europe LLC