

DYMO

DYMO[®] Industrial Labels

Label it fast, label it once, label it right.



This product guide contains RS Stock Numbers

Tough, jobsite-tested labels for industrial applications.

Rely on DYMO® Industrial Labels.

DYMO® Industrial labels are tough – jobsite tested and UL recognized.

Thermal transfer printing means labels won't smudge, smear or fade.

Choose up to a 24 mm label width in a broad assortment of materials and colours that meet OSHA, ANSI, and ISO standards.

All DYMO® Industrial labels are distributed from an easy-to-load cartridge, and with a split-back design, peeling and applying is quick and easy.

DYMO® Industrial labels help you get labelling jobs done fast, and done right – the first time.



DYMO® Industrial Labels are available in:

Flexible Nylon
Permanent Polyester
Indoor/Outdoor Vinyl
Heat-Shrink Tube
Non-Adhesive Tag
Self-Laminating




Labels



DYMO® Industrial Label Benefits:

- 1 Industrial-strength adhesives resist moisture, extreme temperatures, UV light and more – so labels won't curl or fall off
- 2 Available in a range of UL recognized materials for virtually every industrial labelling application; heat-shrink tubes tested to SAE, ASTM and military specifications
- 3 Thermal transfer printing technology – label text won't smudge, smear, or fade
- 4 Choose from 6, 9, 12, 19, and 24 mm label widths in a broad colour assortment that meet OSHA, ANSI, and ISO standards
- 5 Easy-to-peel split back design makes applying labels quick and easy

The right label for virtually every situation and surface.



Indoor/Outdoor Vinyl

For general labelling or extreme conditions. Vinyl labels offer moisture, chemical and UV resistance, making them ideal for labelling both indoors and outdoors. Available in the widest range of colours that adhere to OSHA, ANSI and ISO colour standards.

UL recognized as a component to UL 969

Flexible Nylon

For labelling wires, cables and rounded surfaces. Flexible Nylon labels conform and stick tightly to wires, cables, curved and textured surfaces. Tear-proof material resists damage when pulled through tight spaces or conduits.

UL recognized as a component to UL 969

Permanent Polyester

For labelling panels, blocks, faceplates, shelves, bins, beams and more. Permanent Polyester labels have a polished finish that leaves your work looking professional. Available in smaller widths that fit most patch panels, blocks and other distribution panels.

UL recognized as a component to UL 969

Heat-Shrink Tube

For high-end cable identification. A 3:1 shrink ratio helps ensure a secure fit on wires and cables. Print directly on Heat-Shrink Tubes with any DYMO® Industrial labelling tool.

Meets MIL-M-81531, MIL-STD-202G, SAE-DTL- 23053/5 (Class 1 & 3)
UL recognized as a component to UL 224

Non-Adhesive Tag

For sliding into racks or faceplates that do not require adhesive. Made from polyester for increased durability.

Self-Laminating

Self-Laminating labels protect your printed area from exposure to oil, solvents, water and abrasion when applied to wires and cables.

All DYMO® Industrial labels are RoHS compliant.


For technical specifications on all DYMO® Industrial label types, please visit our website at:
www.dymo.com/industrial

How to choose the right DYMO® Industrial label:

ENVIRONMENT							
SURFACE		Heat/Cold Resistant	UV Light Resistant	Oil Resistant	Water Resistant	Chemical Resistant	Colour Coding
 Cable/Wire	Flexible Nylon Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl
 Curved Surface	Flexible Nylon Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl Flexible Nylon	Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl Flexible Nylon	Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl
 Flat Surface	Permanent Polyester Flexible Nylon	Permanent Polyester Indoor/Outdoor Vinyl	Permanent Polyester Indoor/Outdoor Vinyl	Permanent Polyester Indoor/Outdoor Vinyl	Permanent Polyester Indoor/Outdoor Vinyl	Permanent Polyester Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl
 Textured Surface	Permanent Polyester Flexible Nylon	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl

Top = Best Option Bottom = Alternate Option

Available DYMO® Industrial label widths and colours:



IND	LABEL APPLICATIONS	LABEL COLOUR	Width				
			6 mm	9 mm	12 mm	19 mm	24 mm
Labels that stick and stay stuck. DYMO® Industrial labels are tough— jobsite tested and UL recognized. Labels won't smear or fade and are built with industrial-strength adhesives to resist moisture, UV light and extreme temperatures. Whether you are labelling to OSHA, ISO and ANSI colour standards or labelling in harsh conditions, DYMO® Industrial labels have you covered. DYMO® Industrial labels are designed to work exclusively with Rhino™ printers and to perform on a variety of surfaces. LEARN MORE: www.dymo.com/industrial	BLACK ON WHITE – 4780277 4780283 4780299 7457759	–	–	–	–	–	
		–	–	–	–	–	
		–	–	–	–	–	
		–	–	–	–	–	
		–	–	–	–	–	
		–	–	–	–	–	
		–	–	–	–	–	
VINYL - UL Recognized Component to UL969 - RoHS compliant Length 5.5 m 	BLACK ON YELLOW – – 4780148 4780160 7457740	–	–	–	–	–	
	BLACK ON ORANGE – – 4780182 4780198 7457743	–	–	–	–	–	
	BLACK ON GREY – – 7457706 7457721 7457753	–	–	–	–	–	
	WHITE ON RED – – 7457692 7457719 7457747	–	–	–	–	–	
PERMANENT POLYESTER - UL Recognized Component to UL969 - RoHS compliant Length 5.5 m 	WHITE ON BLACK – 7457699 7457715 7457731 7457778	–	–	–	–	–	
	WHITE ON GREEN – – 7457696 7457728 7457756	–	–	–	–	–	
	WHITE ON BLUE – – 7457709 7457725 7457762	–	–	–	–	–	
HEAT SHRINK TUBES - UL Recognized Component to UL224 - Meets MIL-STD-202G, MIL-M-81531 & SAE-DTL 23053/5 (Class 1 & 3) - RoHS compliant Length 1.5 m 	WHITE ON PURPLE – – 7457703 7457734 7457765	–	–	–	–	–	
	WHITE ON BROWN – – 7457712 7457737 7457769	–	–	–	–	–	
FLEXIBLE NYLON - UL Recognized Component to UL969 - RoHS compliant Length 3.5 m 	BLACK ON WHITE 7457668 4780069 4780075 4780081 522282	–	–	–	–	–	
	BLACK ON CLEAR 7457670 4780306 7457674 7457683 7457680	–	–	–	–	–	
	BLACK ON METALLIC 7457677 4780104 4780110 4780126 7457686	–	–	–	–	–	
NON-ADHESIVE TAG - RoHS compliant Length 5.5 m 	BLACK ON WHITE 5156760 7335883 5155565 5156782 7951356	–	–	–	–	–	
	BLACK ON YELLOW 5156798 5156805 5156827 5156833 7951365	–	–	–	–	–	
FLEXIBLE NYLON - UL Recognized Component to UL969 - RoHS compliant Length 3.5 m 	BLACK ON WHITE – – 4780025 4780031 522294	–	–	–	–	–	
	BLACK ON YELLOW – – 4780047 4780053 522272	–	–	–	–	–	
SELF-LAMINATING - RoHS compliant Length 5.5 m 	BLACK ON WHITE 18111 – 18113 – –	–	–	–	–	–	
	BLACK ON WHITE – – – – 522298	–	–	–	–	–	

For more information or to find out your nearest distributor, please visit www.dymo.com/industrial or call us at +44 (0) 20 7341 5529.



©2018 Newell Brands
 Newell Europe Sàrl
 Chemin de Blandonnet 10
 1214 Vernier - Switzerland